

3 PLACES INDICATED

WINDOW

DATUM PLANE 'E'

13.500±0.150

2X 0.400

4 $\phi 3.065 \pm 0.050$

14.900

A1

3X $\phi 4.000$

0.700±0.070

0.350±0.035

4

2.565±0.050

27.000±0.270

25.250 MAX

7

1.915 MIN

7

A2

A3

14.900±0.150

4.000

21.800



29.800±0.300


DATUM PLANE 'F'

ENCAPSULANT ALLOWED ON CERAMIC AREA


7

VIEW B
DATUMS AND ENCAPSULANT ALLOWABLE AREA
SCALE 8/1





VIEW E (SHEET 1)
DMD WINDOW AND ACTIVE ARRAY
SCALE 12:1



VIEW F-F (SHEET 1)
PINS AND SYMBOLIZATION PAD
SCALE 8/1

DETAIL G (350 PLACES)
PIN & BRAZE DIMENSIONS
SCALE 40/1