

8

7

6

5

4

3

DWG NO. 2516402

SH 3

1

D

D

C


C

B


B

A


A



VIEW D
ENCAPSULANT MAXIMUM X/Y DIMENSIONS [5]
(FROM SHEET 1)



VIEW E
MAXIMUM ENCAPSULANT HEIGHT



8

7

6

5

4

3

2

1

