

8

7

6

5

4

3

DWG NO. 2518330

SH 3

1

D

D

C


C

B


B

A


A



VIEW D
ENCAPSULANT MAXIMUM X/Y DIMENSIONS [5]
(FROM SHEET 1)



VIEW E
MAXIMUM ENCAPSULANT HEIGHT



8

7

6

5

4

3

2


1

D


C

B


A



VIEW E
WINDOW AND ACTIVE ARRAY
(FROM SHEET 1)



DETAIL F
APERTURE TOP EDGE
(GLASS OMITTED FOR CLARITY)
SCALE 60 : 1



DETAIL G
APERTURE BOTTOM EDGE
(GLASS OMITTED FOR CLARITY)
SCALE 60 : 1

