

8		7		6		5		4		3		DWG NO 2503731SH 1		1																	
NOTES: UNLESS OTHERWISE SPECIFIED: 1. BEND RADII .76 [.03] MAX 2 TANGENT POINT DIMENSION 3 BURR SIDE FOR ALL PERIPHERY AND PIERCED HOLES 4 GRAIN DIRECTION 5. NO VISIBLE CRACKING PERMITTED										© COPYRIGHT 2001 TEXAS INSTRUMENTS UN- PUBLISHED, ALL RIGHTS RESERVED.		REVISIONS																			
										REV	DESCRIPTION		DATE		UPDATED BY																
										A	ECO 5389 - INITIAL RELEASE		01/10/17		DH																
																AR		I		.020 INCH THK 301 STAINLESS STEEL , 1/2 HARD											
																-1		ITEM		PART OR IDENTIFYING NUMBER				NOMENCLATURE OR DESCRIPTION				NOTES			
																QTY		NO													
																UNLESS OTHERWISE SPECIFIED • DIMENSIONS ARE IN MILLIMETERS • TOLERANCES: ANGLES ± 1° 2 PLACE DECIMALS ±0.25 1 PLACE DECIMALS ±0.50 • DIMENSIONAL LIMITS APPLY BEFORE PROCESSES • INTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994 • REMOVE ALL BURRS AND SHARP EDGES • PARENTHETICAL INFO FOR REF ONLY						DWN		DATE		TEXAS INSTRUMENTS <i>Dallas, Texas</i> SPRING, STUD RETAINER, TOLERANCE CONTROL MOUNT METHOD					
																						ENGR		DATE							
																						QA		DATE							
																						APVD		DATE							
																						2503737		0314GP		J. MCKINLEY		01/10/19		T. DOTY	
																NEXT ASSY		USED ON		APPLICATION		SIZE		DRAWING NO		REV					
																						D		2503731		A					
						SCALE		SHEET																							
						4/1		1 OF 3																							



