

NOTES: UNLESS OTHERWISE SPECIFIED:

© COPYRIGHT 2001 TEXAS INSTRUMENTS UN-
PUBLISHED, ALL RIGHTS RESERVED.

REVISIONS			
REV	DESCRIPTION	DATE	UPDATED BY
A	ECO 5605 – INITIAL RELEASE	01/12/05	DH

D

D

C



C

B

B


A

A



DETAIL A

SCALE: 10X

AR	I	.093 THK FR-4				
-1	ITEM	PART OR IDENTIFYING NUMBER	NOMENCLATURE OR DESCRIPTION	NOTES		
QTY	NO					
PARTS LIST						
	<div>UNLESS OTHERWISE SPECIFIED</div> <ul style="list-style-type: none">DIMENSIONS ARE IN MILLIMETERS [INCHES]TOLERANCES: ANGLES $\pm 1^\circ$ 2 PLACE DECIMALS ± 0.25 1 PLACE DECIMALS ± 0.50DIMENSIONAL LIMITS APPLY BEFORE PROCESSESINTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994REMOVE ALL BURRS AND SHARP EDGESPARENTHETICAL INFO FOR REF ONLY	DWG HOLAMON			DATE 01/12/05	<div><div>TEXAS INSTRUMENTS <i>Dallas, Texas</i></div><div>MOCK PWB, TOLERANCE CONTROL MOUNT METHOD</div></div>
		ENGR J. MCKINLEY			01/12/06	
0314GP		QA J. KNOX			01/12/06	
0314GP		APVD J. ATCHISON	01/12/06			
USED ON						
LOCATION		SIZE D	DRAWING NO 2503867	REV A		
		SCALE 2/1	SHEET 1 OF 2			

- UNLESS OTHERWISE SPECIFIED
- DIMENSIONS ARE IN MILLIMETERS [INCHES]
 - TOLERANCES: ANGLES ± 1°
2 PLACE DECIMALS ±0.25
1 PLACE DECIMALS ±0.50
 - DIMENSIONAL LIMITS APPLY BEFORE PROCESSES
 - INTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994
 - REMOVE ALL BURRS AND SHARP EDGES
 - PARENTHEetical INFO FOR REF ONLY

DWG	DATE
HOLAMON	01/12/05
ENGR	DATE
J. MCKINLEY	01/12/06
QA	DATE
J. KNOX	01/12/06
APVD	DATE
J. ATCHISON	01/12/06

SIZE	D	DRAWING NO	2503867	REV	A
SCALE	2/1	SHEET	1 OF 2		

