

8

7

6

5

4

3

DWG NO. 2507517

SH 1



1

NOTES: UNLESS OTHERWISE SPECIFIED:

- 1. BEND RADIUS 0.06
- 2. BEND RELIEF SHOP OPTION

© COPYRIGHT 2006 TEXAS INSTRUMENTS
UN-PUBLISHED, ALL RIGHTS RESERVED.

REV		DESCRIPTION	DATE	UPDATED BY
A		ECO #2066944 - INITIAL RELEASE	02-22-2006	JTM



2507519	0314RD
NEXT ASSY	USED ON
APPLICATION	

UNLESS OTHERWISE SPECIFIED

- DIMENSIONS ARE IN MILLIMETERS
- TOLERANCES:
- ANGLES ± 1°
- 2 PLACE DECIMALS ± 0.25
- 1 PLACE DECIMALS ± 0.50
- DIMENSIONAL LIMITS APPLY BEFORE PROCESSES
- INTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994
- REMOVE ALL BURRS AND SHARP EDGES
- PARENTHETICAL INFORMATION FOR REFERENCE ONLY

DRAWN	DATE
McKINLEY	2/22/2006
ENGINEER	
J. McKINLEY	3/1/2006
QA/CE	
C. LOWELL	3/1/2006
CM	
D. HOLAMON	3/3/2006
APPROVED	
J. McKINLEY	3/1/2006

 TEXAS INSTRUMENTS <small>Dallas, Texas</small>	
TITLE	
BRACKET, HEATSINK TO PC BOARD	
SIZE	D
DWG NO	2507517
REV	A
SCALE	1:1
SHEET	1 OF 1