

REV	DESCRIPTION	DATE	BY
A	INITIAL RELEASE	9/15/2014	JTM

NOTES: UNLESS OTHERWISE SPECIFIED:



- 1 EXAMPLE DIMENSION - EXACT DIMENSION WILL VARY BASED UPON THE OPTICAL DESIGN AND ARRAY SIZE
- 2 SURFACE CONDITION AND FINISH NEAR OPENING VERY CRITICAL FOR OPTICAL PERFORMANCE

D

C

B

A



AR	QTY	ITEM	PART NUMBER	DESCRIPTION	Notes
1	-	-	0.203 mm (.008 INCH) THK STAINLESS STEEL, ALY 301		

<p>UNLESS OTHERWISE SPECIFIED</p> <ul style="list-style-type: none"> • DIMENSIONS ARE IN MILLIMETERS • TOLERANCES: ANGLES ±1° 2 PLACE DECIMALS ±0.25 1 PLACE DECIMALS ±0.50 • DIMENSIONAL LIMITS APPLY BEFORE PROCESSES • INTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994 • REMOVE ALL BURRS AND SHARP EDGES • PARENTHETICAL INFO FOR REF ONLY 		<p>DWN J. MCKINLEY Engr</p> <p>DATE 9/14/2014</p> <p>CQE/QA</p> <p>CM</p> <p>Apprvd MCKINLEY</p> <p>DATE 9/15/2014</p>	<p>TEXAS INSTRUMENTS</p> <p>APERTURE, SERIES 600 SYSTEM</p> <p>SIZE B</p> <p>DWG NO 2511727</p> <p>REVISION A</p> <p>SCALE 2:1</p> <p>SHEET 1 OF 1</p>
<p>2511654</p> <p>NEXT ASSY</p>	<p>0314RD</p> <p>USED ON</p>	<p>APPLICATION</p>	

