






NOTES: UNLESS OTHERWISE SPECIFIED:

© COPYRIGHT 2014 TEXAS INSTRUMENTS
UNPUBLISHED, ALL RIGHTS RESERVED

REVISIONS			
REV	DESCRIPTION	DATE	BY
A	INITIAL RELEASE	7/24/2014	JTM



VIEW F-F



AR	1	0.406 mm THICK 301 STAINLESS STEEL, 1/2 HARD		
QTY	ITEM	PART NUMBER	DESCRIPTION	Notes
Part List				
		<div>UNLESS OTHERWISE SPECIFIED</div> <ul style="list-style-type: none">DIMENSIONS ARE IN MILLIMETERSTOLERANCES: ANGLES ±1° 2 PLACE DECIMALS ±0.25 1 PLACE DECIMALS ±0.50DIMENSIONAL LIMITS APPLY BEFORE PROCESSESINTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994REMOVE ALL BURRS AND SHARP EDGESPARENTHETICAL INFO FOR REF ONLY		
2513792	0314RD	<div>TEXAS INSTRUMENTS</div> <div>SPRING, FLAT</div>		
NEXT ASSY	USED ON			
APPLICATION		Part List		
		DWN J. McKinley	DATE 7/4/2013	<div>TEXAS INSTRUMENTS</div> <div>SPRING, FLAT</div>
		Engr		
		CQE/QA		
		CM		
		Apprvd McKinley	7/24/2014	SCALE 2:1
		SIZE B	DWG NO 2513988	REV A
		SHEET 1 OF 1		