

H.264 High Profile Decoder (v01.10.05) on DM6467

FEATURES

- eXpressDSP™ Digital Media (XDM 1.0 IVIDDEC2) compliant
- Up to level 4 features of the High Profile (HP) supported
- Validated on DM6467 EVM
- Progressive, interlaced, Picture Adaptive Frame Field (PicAFF) and Macro-block Adaptive Frame Field (MBAFF) type picture decoding supported
- Multiple slices and multiple reference frames supported
- CAVLC and CABAC decoding supported
- All intra-prediction and inter-prediction modes supported
- Up to 16 MV per MB supported
- Frame based decoding supported

- Picture width greater than 64 pixels supported
- Tested for compliance with JM version 10.1 reference decoder
- Long term reference frame and adaptive reference picture marking supported
- Reference picture list reordering supported
- PCM macro block decoding supported
- Gaps in frame_num supported
- Error resiliency and concealment supported
- SEI and VUI parsing supported

DESCRIPTION

H.264 is a popular video coding algorithm enabling high quality multimedia services on a limited bandwidth network. H264 Decoder is validated on DM6467 EVM with Code Composer Studio version 3.3.49 and code generation tools version 6.0.8.

PRODUCT PREVIEW



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

eXpressDSP is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

Performance Summary

This section describes the performance of the H264 Decoder on DM6467 EVM.

Table 1. Configuration Table

CONFIGURATION	ID
H264 High Profile Decoder	DM6467_HP_001

Table 2. Cycles Information in MHz - Profiled on DM6467 EVM with Code Generation Tools Version 6.0.8

CONFIGURATION ID	PERFORMANCE STATISTICS (MEGA CYCLES PER SECOND)				
	TEST DESCRIPTION	NON-BLOCKING DSP CYCLES@675MHz		BLOCKING DSP CYCLES@675MHz	
		AVERAGE	PEAK	AVERAGE	PEAK
DM6467_HP_001	BALLOONS.264;High Profile, 1920 X 1088, MBAFF, IPBB...	317.76	354.55	568.67	595.32
	fball_60.264;High Profile, 1920 X 1088, MBAFF, IPBB...	331.32	351.58	581.69	594.57
	letterman1_30.264; High Profile, 1920 X 1088, MBAFF, IPBB...	332.58	351.9	581.86	593.96

Table 3. Memory Statistics - Generated with Code Generation Tools Version 6.0.8

CONFIGURATION ID	MEMORY STATISTICS				
	PROGRAM MEMORY	DATA MEMORY			TOTAL
		INTERNAL	EXTERNAL	STACK	
DM6467_HP_001 (176 x 144)	300.38	22.63	2425.20	4.00	2752.21
DM6467_HP_001 (320 x 240)	300.38	22.63	3591.08	4.00	3918.09
DM6467_HP_001 (352 x 288)	300.38	22.63	4151.33	4.00	4478.34
DM6467_HP_001 (640 x 480)	300.38	22.63	8511.83	4.00	8838.84
DM6467_HP_001 (720 x 480)	300.38	22.63	9268.83	4.00	9595.84
DM6467_HP_001 (720 x 480)	300.38	22.63	10782.83	4.00	11109.84
DM6467_HP_001 (1280 x 720)	300.38	22.63	13053.95	4.00	13380.96
DM6467_HP_001 (1920 x 1088)	300.38	22.63	14315.70	4.00	14642.71
DM6467_HP_001 (1088 x 1920)	300.38	22.63	14701.58	4.00	15028.59

Table 4. Internal Data Memory Split-Up

CONFIGURATION ID	DATA MEMORY - INTERNAL		
	SHARED		INSTANCE
	CONSTANTS	SCRATCH	
DM6467_HP_001	0	22.63	0

Table 5. External Data Memory Split-Up

CONFIGURATION ID	DATA MEMORY - EXTERNAL		
	SHARED		INSTANCE
	CONSTANTS	SCRATCH	
DM6467_HP_001	207.70	0	23936.42

Notes

The performance values shown in is a result of the following configurations:

- HDVICP
 - The entire HDVICP is a video resource and uses 16K ITCM and 8K DTCM.
 - The decoder is configured to run either on HDVICP-0 or HDVICP-1.
- Cache configuration

Table 6. Cache Configuration

	AVAILABLE	USED
L1 p (Program Memory)	32K	32K – cache
L1d (Data Memory)	32K	32K – cache
L2	128K	64K – cache

- DMA configuration

Table 7. DMA Configuration

TC Qs	TC 0	TC 1	TC 2	TC 3	TOTAL	MAXIMUM
Usage	Writes to L2 SRAM	Writes to HDVICP	Writes to HDVICP	Writes to HDVICP	-	-
Priority	3	2	2	3	-	-
EDMA channels	1	8	8	4	21	64
QDMA channels	0	0	0	0	0	8
Num PARAMS	-	-	-	-	159	512

- Code Placement
 All the algorithm code are placed in external memory. The performance values in are sensitive to algorithm code placement. See the sample linker file provided in the test application setup for algorithm code placement.

References

- ISO/IEC 14496-10: March 2005 (E) Rec. H.264 (E) ITU-T Recommendation
- *H.264 High Profile Decoder on DM6467 User's Guide* (literature number: SPRUFE0E)

Glossary

TERM	DESCRIPTION
Constants	Elements that go into .const memory section
Scratch	Memory space that can be reused across different instances of the algorithm
Shared	Sum of Constants and Scratch
Instance	Persistent-memory that contains persistent information - allocated for each instance of the algorithm

Acronyms

ACRONYM	DESCRIPTION
625SD	Level 3.0 Maximum resolution format size 720x576
CIF	Common Intermediate Format
CPB	Coded Picture Buffer
D1	SDTV image resolution (720x480)
DMA	Direct Memory Access
EVM	Evaluation Module
HD	High Definition
HDVICP	High Definition Video and Imaging Co-Processor
MBAFF	Macro Block Adaptive Frame Field
PCM	Pulse Code Modulation
PicAFF	Picture Adaptive Frame Field
QCIF	Quarter Common Intermediate Format
QDMA	Quick Direct Memory Access
SDTV	Standard Definition Television
SEI	Supplemental Enhancement Information
SRAM	Static Random Access Memory
VGA	Video Graphics Array (640x480 resolution)
VUI	Video Usability Information
XDM	eXpressDSP Digital Media