




NOTES: UNLESS OTHERWISE SPECIFIED:

1 CENTER POSITION OF THE CONTACT AREA IN THE COMPRESSED STATE

2 HEIGHT WHEN CONTACTS ARE FULLY COMPRESSED BETWEEN DMD AND PCB

© COPYRIGHT 2014 TEXAS INSTRUMENTS
UNPUBLISHED, ALL RIGHTS RESERVED

REVISIONS			
REV	DESCRIPTION	DATE	BY
A	INITIAL FORMAL RELEASE	2/05/2014	JTM
B	IDENTIFIED MISSING DATUM 'C'	3/16/2014	JTM



UNLESS OTHERWISE SPECIFIED


- DIMENSIONS ARE IN MILLIMETERS
- TOLERANCES: ANGLES ±1°
2 PLACE DECIMALS ±0.25
1 PLACE DECIMALS ±0.50
- DIMENSIONAL LIMITS APPLY BEFORE PROCESSES
- INTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994
- REMOVE ALL BURRS AND SHARP EDGES
- PARENTHETICAL INFO FOR REF ONLY

DWN
J. MCKINLEY
Engr
MCKINLEY
CQE/QA
CM
Apprvd
J. MCKINLEY
DATE
1/9/2014
2/5/2014
SHEET
1 OF 2



INTERPOSER, 1080P SERIES 312

SIZE
B
DWG NO
2513791
REV
B
SCALE 2:1
SHEET 1 OF 2



0314RD
NEXT ASSY
USED ON
APPLICATION

D

C

B


A

D


C

B

A



VIEW A - PCB SIDE



DETAIL F
SCALE 16 : 1