

## MPEG2 Main Profile Decoder (v1.10.00) on DM6467

### FEATURES

- eXpressDSP™ Digital Media (XDM 1.2 IVIDDEC2) complaint
- Validated on DM6467 EVM
- All I, P, and B frame decoding supported
- Both progressive and interlaced supported
- Outputs are available in YUV 420 interleaved formats (Y in one plane and U and V data interleaved to form the other plane)
- Frame based decoding with frame size being multiples of 16 supported
- Simple Profile MPEG2 decoding supported
- Main Profile MPEG2 decoding supported
- DMA based framework supported
- Use of C64x+ and ARM968 of HD-VICP0 and

### HDVICP1 supported

- Interrupt based communication between processors supported
- Bottom field optimization option added for B Frames
- Output frames are available in display and decode order
- DeBlocking and Deringing supported

### DESCRIPTION

MPEG2 video standard specifies the decompression and coded representation for entertainment-quality digital video. It is validated on DM6467 EVM, with Code Composer Studio version 3.3.49, and code generation tools version 6.0.16.

**PRODUCT PREVIEW**



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

eXpressDSP is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

PRODUCT PREVIEW information concerns products in the formative or design phase of development. Characteristic data and other specifications are design goals. Texas Instruments reserves the right to change or discontinue these products without notice.

Copyright © 2010, Texas Instruments Incorporated

## Performance Summary

This section describes the performance of the MPEG2 Decoder on DM6467 EVM.

**Table 1. Configuration Table**

CONFIGURATION	ID
Mpeg2 Main Profile at High Level (no De-blocking)	DM6467_MP_001
Mpeg2 Main Profile at High Level (with De-blocking + De-ringing)	DM6467_MP_002

**Table 2. Cycles Information in MHz - Profiled on DM6467 EVM with Code Generation Tools Version 6.0.16**

CONFIGURATION ID	PERFORMANCE STATISTICS (MEGA CYCLES PER SECOND) <sup>(1)</sup> <sup>(2)</sup>				
	TEST DESCRIPTION	DSP CYCLES AT 600 MHZ		HDVICP ARM 968 CYCLES AT 300 MHz	
		AVERAGE	PEAK <sup>(3)</sup>	AVERAGE	PEAK <sup>(3)</sup>
DM6467_MP_001	1080i25_shields_ter_1920x1080_420_bf.m2v	6.4	6.8	246	259
	1080i25_stockholm_ter_1920x1080_420_bf.m2v	6.4	6.8	240	253
	mobcal_ter_1920x1080_420_br_3_10.m2v ( B-Frames in sequence)	6.3	6.7	263	314
DM6467_MP_002	1080i25_shields_ter_1920x1080_420_bf.m2v	6.7	7.0	273	280
	1080i25_stockholm_ter_1920x1080_420_bf.m2v	6.7	7.0	267	274
	mobcal_ter_1920x1080_420_br_3_10.m2v ( B-Frames in sequence) DSP cycles at 600 MHz	6.6	7.0	292	336

- (1) Measured with program memory, stack, and I/O buffers in external memory and with cache configuration 32 K bytes L2 cache, 32 K L1D cache and 32 K L1P cache.  
(2) Average and peak MCPS measurements can vary by +/-5%.  
(3) Peak values are calculated assuming that the most demanding frame is repeated 30 times in the sequence, rather than finding the most demanding 30 frames sequence in the bit-stream.

**Table 3. Memory Statistics - Generated with Code Generation Tools Version 6.0.16**

CONFIGURATION ID	MEMORY STATISTICS <sup>(1)</sup>				TOTAL
	PROGRAM MEMORY	DATA MEMORY			
		INTERNAL <sup>(2)</sup>	EXTERNAL <sup>(2)</sup>	STACK	
DM6467_MP_001 DM6467_MP_002	59.5	32	29.4	2	123.3

- (1) All memory requirements are expressed in kilobytes (1K-byte = 1024 bytes).  
(2) Internal memory is placed in L2 SRAM.

**Table 4. Internal Data Memory Split-Up**

CONFIGURATION ID	DATA MEMORY - INTERNAL <sup>(1)</sup>		
	SHARED		INSTANCE
	CONSTANTS	SCRATCH	
DM6467_MP_001 DM6467_MP_002	0	32	0

- (1) All memory requirements are expressed in kilobytes

**Table 5. External Data Memory Split-Up**

CONFIGURATION ID	DATA MEMORY - EXTERNAL <sup>(1)</sup>		
	SHARED		INSTANCE
	CONSTANTS	SCRATCH	
DM6467_MP_001 DM6467_MP_002	0.50	0	27.76

(1) All memory requirements are expressed in kilobytes.

## Notes

The performance values in tables 2, 3, and 4 is a result of the following configuration:

- HDVICP
  - The entire HDVICP is a video resource and uses 16K ITCM and 8K DTCM.
  - The decoder is configured to run on either HDVICP-0 or HDVICP-1
- Cache configuration

**Table 6. Cache Configuration**

	AVAILABLE	USED
L1 P (Program Memory)	32K	32K - cache
L1 D (Data Memory)	32K	32K - cache
L2	128K	32K - cache

- DMA configuration

**Table 7. DMA Configuration**

TC Q's	TC 0	TC 1	TC 2	TC 3	TOTAL
Usage	Writes to L2	Not used	Writes to HDVICP and DDR	Writes to HDVICP and DDR	
Priority	2 (default)	-	2 (default)	2 (default)	
EDMA Channels	1	-	7	9	17/64
QDMA Channels	0	-	0	0	0/8
Num PARAMs	-	-	-	-	168/512

- Code placement  
All the algorithm code are placed in external memory. The performance values in table 2, 3, and 4 are sensitive to algorithm code placement. See the sample linker file provided in the test application setup for algorithm code placement.

## References

- *MPEG2 Main Profile Decoder on DM6467 User's Guide* (literature number - SPRUFE1A)

## Glossary

TERM	DESCRIPTION
Constants	Elements that go into .const memory section
Scratch	Memory space that can be reused across different instances of the algorithm
Shared	Sum of Constants and Scratch
Instance	Persistent-memory that contains persistent information - allocated for each instance of the algorithm

## Acronyms

ACRONYM	DESCRIPTION
CPB	Constrained Parameters Bit-streams
DMA	Direct Memory Access
DMAN3	DMA Manager
EVM	Evaluation Module
IDCT	Inverse Discrete Cosine Transform
MCPS	Mega Cycles Per Second
MPEG	Motion Picture Expert Group
QDMA	Quick Direct Memory Access
XDM	eXpressDSP Digital Media

## Revision History

This Data sheet revision history highlights the changes made to the SPRS481A codec specific Data sheet to make it SPRS481B.

**Table 8. Revision History for MPEG2 Main Profile Decoder on DM6467**

SECTION	CHANGES
<a href="#">Table 7</a>	<ul style="list-style-type: none"> <li>Modified DMA Configuration values</li> </ul>

**PRODUCT PREVIEW**

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

<b>Products</b>		<b>Applications</b>	
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>	Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>	Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>	Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>	Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>	Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>	Energy	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>	Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>	Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>	Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>	Space, Avionics & Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
RF/IF and ZigBee® Solutions	<a href="http://www.ti.com/lprf">www.ti.com/lprf</a>	Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
		Wireless	<a href="http://www.ti.com/wireless-apps">www.ti.com/wireless-apps</a>

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2010, Texas Instruments Incorporated