


DLP2021LEQ1EVM Optical Design Overview

Disclaimer


- Please use this document as a reference design only, changes might apply to a later version.
- No Tolerance Analysis or Thermal analysis has been done on this design.

Optical Specification Target


- 0.2" DLP chip (588x330) – DLP2021-Q1
- Throw Ratio: 2.4~
 - Image Diagonal:
 - 400 mm (projection distance 850 mm)
 - 470 mm (projection distance 1000 mm)
 - 540 mm (projection distance 1150 mm)
- F/3 - for no focus adjustment through projection distance 850-1150mm
- Power to the LED : ~1.5 W
- Engine Efficiency: 23.8lm/W (estimated with current preliminary data)
- Size: 30.8mm x 24.5mm x 9mm
- Resolution: 2 Pixels length
 - (grouping 2x2 pixels as the smallest fixture to be resolved, since it will be projected on concrete ground, image quality does not need to be high)




Luminus SFT/SFM-03X Chipset Overview



SFT-03X-CG



SFM-03X-RB



SFT-03X-W


- Emitting area $0.75 \times 0.46 \text{ mm}^2$ (0.345 mm^2) for all colors
- Etendue-matched to DLP2021 Automotive DMD at f/3.0
- Engine configurations:
 - Full color RGB engine (2 channels)
 - White (1 channel)
 - Monochromatic Red for future consideration (contact Luminus)
- Large dynamic range: CG, B up to 1.75A; RA, White up to 1.4A
 - Typical drive current in DGP applications: ~ 500 mA (1.5W)
- Package: Prototypes in 3.0 mm x 3.0 mm SMT package.
 - Isolated thermal pad with high thermal conductivity
- Automotive Qualification in progress

SFT/SFM-03X Performance

	 CG	 RA	 B	 W
Optical Output @ 0.5A	205 lm	72 lm	0.65W	150 lm
Forward Voltage @ 0.5A	3.10V	2.5V	3.10V	3.10V
Dom. Wavelength (W: CCT)	554 nm	612 nm	453 nm	6000K typ


All parametric values are typical values for initial engineering samples at single 20 ms pulse, 25C ambient test condition

System layout




DMD

$29.0\text{mm} \times 36.6\text{mm} \times 12.2\text{mm} = 12.9\text{cc}$



Optical System Performance


Uniformity at image plane



- Geometric Efficiency
- RGB 73% / 74.9% / 69%


Image Diagram	
11/16/2021 Image Width = 400.0000 Millimeters, 500 x 500 pixels Field position: 0.0000, 0.0000 mm Percent efficiency: 72.376%, 7.238E-01 Watts Surface: 61. Units are watts per Millimeters squared.	Zemax Zemax OpticStudio 19.4 SP1 20210621 02inch Ground projector EVM-2.zmx Configuration: All 3

Projection Lens






- All surfaces are spherical
- Material Used left to right (Schott Preferred)
 - H-ZLAF52
 - H-ZF52
 - H-LAK53B
 - H-ZF52
 - Telecentric @ DMD

Distortion & MTF



11/16/2021 Field: 3.65 w 2.05 h Millimeters Image: 281.39 w 158.28 h Millimeters Maximum distortion: 1.5167% SMIA TV distortion: 1.1582% Scale: 1.000X, wavelength: 0.5876 μm	Zemax Zemax OpticStudio 19.4 SP1 20210621 02Inch Ground projector lens.zos Configuration 1 of 3
--	--



Estimated Lumens Budget

Illumination	Luminus SFT-03		
DMD	DLP2021-Q1 (0.2" 588x330)		
	TI assumption		
	Efficiency factor	Lumens	Comments
Lumens out of color balanced LED		134	Estimated D65 White lumens at 1.5W LED Electrical Power, 60C board.
Transmission			
Collimator lenses	0.96	129	Transmission – AR coating losses
Dichroic Filters	0.91	117	Losses due to filtering
Fly's Eye	0.93	109	Fly's Eye estimated transmission
Illumination relay lens	0.98	107	AR coating loss
Field Lens	0.96	102	Two path, illumination + projection
Avg DMD efficiency	0.67	69	DMD efficiency (Mirror reflectivity + diffraction + fill + Transmission)
Projection Fold	0.97	67	
Projection lens (3 lenses)	0.94	63	Transmission of projection lens from coatings, field lens loss already calculated above
transmission overall efficiency (avg)	0.47	63	
geometric overall efficiency	0.72	45	
sequence efficiency	0.87	39	Automotive sequence ~87% due to multipulse
overall efficiency (avg)	0.28		
Total Lumens		39	Max brightness achievable (estimated)
System efficiency achieved (lm/Welec)		26.1 lm/W	Efficiency may be higher at lower lumen levels