

MPEG4 Restricted Simple Profile Decoder (v01.10.00) on DM365

FEATURES

eXpressDSP™ Digital Media (XDM 1.0 IVIDENC2) interface and IRES compliant
Validated on DM365 EVM with Monta Vista® Linux® 5.0

MPEG4 simple profile levels 0, 1, 2 and 3 are supported with the following limitations:

- No support for 4 MV
- No support for MV ranges beyond -32 to 31
- No support for Data partitioning (DP) and Reversible VLCs (RVLCs)

Decodes the following formats:

- VGA (640 x 480)
- D1 (720 x 480)
- 720P (1280 x 720)
- SXVGA (1280 x 960)
- 1080p (1920x1080)

Half Pel Interpolation (HPI) for motion estimation supported

One motion vector encoding for motion estimation (1MV/MB) with (-32, +31) half pel search range supported

Streams with DC and AC prediction supported

Streams with Resync Marker (RM) supported

Streams with Short Video Header (SVH) supported

YUV 4:2:2 interleaved data as an output supported

YUV 4:2:0 semi-planar (NV12 format, that is, Y planar, Cb Cr interleaved) data as an output supported

Display width can be greater than the image width.

Supports rotation (90, 180 and 270 degrees) integrated with the Decoder for certain image formats such as QVGA (320x240), VGA (640x480), 720P (1280x720), and SXVGA

(1280x960). Also supports rotation of 240x320 (rotated QVGA) and 480x640 (rotated VGA)

Unrestricted Motion Vectors (UMV) supported

Decodes all DM365 encoded streams

Decodes streams of VBR, CBR, and CVBR rate control

Frame level re-entrancy supported

Multi-instance of MPEG4 Decoder, and single/multi instance of MPEG4 Decoder with other DM365 codecs supported

Decodes only those streams encoded with the DM365 MPEG4 Encoder.

This decoder does not support the following:

- Video packet resynchronization
- Header extension code (HEC)
- AC prediction for varying Qp (rateFix = 0)
- Arbitrary width and height.
 - Image width as multiple of 16 and height as multiple of 16 supported
 - Image width below 160 and 192 for YUV 422ILE and YUV 420SP format respectively is not supported
- Decoding of 720x1280 (rotated 720P) and 960x1280 (rotated SXVGA) formats

DESCRIPTION

MPEG4 is the ISO/IEC recommended standard for video compression. This version of the MPEG4 Simple Profile decoder is a restricted decoder. It can only decode streams encoded by DM365 MPEG4 Encoder. It is validated on DM365 EVM with Monta Vista Linux 5.0.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

eXpressDSP is a trademark of Texas Instruments.

Linux is a registered trademark of Linus Torvalds.

Monta Vista is a registered trademark of MontaVista Software, Inc.

All other trademarks are the property of their respective owners.

Performance Summary

This section describes the performance of the MPEG4 Restricted Simple Profile Decoder on DM365 EVM.

Table 1. Configuration Table

CONFIGURATION	ID
MPEG4 simple profile, I/D Cache Enabled Output Format: XDM_YUV_420SP Rotation 0 ME 31 UMV OFF	MPEG4_DEC_01
MPEG4 simple profile, I/D Cache Enabled Output Format: XDM_YUV_422ILE Rotation 0 ME 31 UMV OFF	MPEG4_DEC_02
MPEG4 simple profile (SVH Mode), I/D Cache Enabled Output Format: XDM_YUV_422ILE Rotation 0 ME 31 UMV OFF	MPEG4_DEC_03 (SVH)

Performance Measurement Procedure

Measured with program memory and I/O buffers in external memory, I/D cache enabled, ARM @297 MHz, MJCP @243 MHz, DDR @243 MHz, Monta Vista Linux 5.0

DVTB is used to measure the performance numbers in this Datasheet.

The process time is measured across algActivate/process/algDeactivate function call using gettimeofday() utility of linux.

NFS File system is used as an environment in performance measurement.

To avoid the impact of file I/O operation in performance measurement, file write operation is disabled and checksum calculation is included after fread() function to make sure file read has really completed before process call.

After rebooting the board, codec binary must be executed at least once before start of performance measurement.

Note: Frame decode load can be divided in ARM load and MJCP load. ARM is idle during MJCP processing, and can be utilized to execute any other program in different thread during this time.

Table 2. Cycles Information for MPEG4_DEC_01

INPUT NAME	RESOLUTION	PERFORMANCE STATISTICS (MEGA CYCLES PER SECOND) ⁽¹⁾					
		AVERAGE			PEAK		
		ARM926 PER FRAME	DECODE PER FRAME	FPS	ARM926 PER FRAME	DECODE PER FRAME	FPS
BUS	CIF (352x288) @512kbps	0.49	1.12	264.11	0.62	1.30	228.71
Coastguard	VGA (640x480) @3mbps	0.53	2.36	125.52	0.59	2.47	120.04
Football	D1 (720x480) @4mbps	0.53	3.15	94.30	0.59	3.24	91.50
Stockholm	720p (1280x720) @8mbps	0.54	6.18	48.01	0.63	6.34	46.82
Pedestrian	SXVGA (1280x960) @10mbps	0.55	8.04	36.93	0.68	8.21	36.17
Ralli	1080p (1920x1080) @16mbps	0.49	16.51	17.99	0.62	16.94	17.53

(1) Average and peak MCPS values may vary by +/-5%.

Table 3. Cycles Information for MPEG4_DEC_02

INPUT NAME	RESOLUTION	PERFORMANCE STATISTICS (MEGA CYCLES PER SECOND) ⁽¹⁾					
		AVERAGE			PEAK		
		ARM926 PER FRAME	DECODE PER FRAME	FPS	ARM926 PER FRAME	DECODE PER FRAME	FPS
BUS	CIF (352x288) @512kbps	0.52	1.15	258.26	0.58	1.23	241.99
Coastguard	VGA (640x480) @3mbps	0.53	2.35	126.33	0.69	2.51	118.21
Football	D1 (720x480) @4mbps	0.53	3.11	95.46	0.62	3.26	91.22
Stockholm	720p (1280x720) @8mbps	0.55	6.03	49.24	0.60	6.11	48.58
Pedestrian	SXVGA (1280x960) @10mbps	0.51	7.80	38.08	1.14	8.46	35.10
Ralli	1080p (1920x1080) @16mbps	0.49	15.95	18.63	0.59	16.40	18.11

(1) Average and peak MCPS values may vary by +/-5%.

Table 4. Cycles Information for MPEG4_DEC_03

INPUT NAME	RESOLUTION	PERFORMANCE STATISTICS (MEGA CYCLES PER SECOND) ⁽¹⁾					
		AVERAGE			PEAK		
		ARM926 PER FRAME	DECODE PER FRAME	FPS	ARM926 PER FRAME	DECODE PER FRAME	FPS
Foreman	CIF (352x288) @512kbps	0.50	1.23	242.42	0.51	1.74	170.72
ICE	2CIF (704x576) @4mbps	0.49	2.87	103.25	0.53	2.96	100.45

(1) Average and peak MCPS values may vary by +/-5%.

Note:

The values in Table 2, 3, and 4 are as measured on the ARM 926 side. These are the actual cycles as seen from the host on the DM365 EVM board and will be close to cycles seen on the final system (for average case).

ARM926 represents mega cycles per frame spend on ARM926.

Decode frame time is the time seen from ARM926 only. Since most of the processing happens at MJCP, the active load on ARM926 is the value mentioned in ARM926 column. Decode frame time has no connection with MJCP running at 243 MHz.

All values are collected (both average and peak) at frame-level processing.

They are measured with Linux without any system traffic.

Table 5. Memory Statistics

RESOLUTION	MEMORY STATISTICS (IN BYTES)					
	PROGRAM MEMORY	DATA MEMORY				TOTAL
		CONSTANT	INTERNAL	EXTERNAL	STACK	
1080p (1920x1080)	101562	4274	0	6882584	8192	6996612
SXVGA (1280x960)	101562	4274	0	4154648	8192	4268676
720P (1280x720)	101562	4274	0	3186968	8192	3300996
D1 (720x480)	101562	4274	0	1305368	8192	1419396
VGA (640x480)	101562	4274	0	1174808	8192	1288836
CIF (352x288)	101562	4274	0	465176	8192	579204

Table 6. Usage of External Memory through CMEM

BUFFER	SIZE	
Input Buffer ⁽¹⁾	frameSize ⁽²⁾ *2	
Output Buffer	YUV_422_ILE	Buffer1: frameSize*2
	YUV_420_SP	Buffer1: frameSize Buffer2: frameSize/2
External Data Memory	memTab[0]	11928
	memTab[1]	3* frameSize_padded ⁽³⁾
	memTab[2]	8640 Bytes
	memTab[3]	8192 Bytes

(1) Input buffer size is theoretical size based on 1:1 compression. Actual input size will be lower than this.

(2) frameSize = (Width * Height).

(3) frameSize_padded = ((Width + 64)*(Height+64))

Notes

The entire MJCP is a video resource and is used by the codec DMA configuration

Table 7. DMA Configuration

TC Q's	TC 0	TC 1	TC 2	TC 3	TOTAL
Usage	Reserved for system	Used by codec	Not used by codec	Not used by codec	-
Priority	0	Not touched by codec (Default – 7)	-	-	-
EDMA Channels	0	31	0	0	31/64
PaRAM Entries	0	47	0	0	47/256
QDMA Channels	0	0	0	0	0/8

The MJCP/EDMA resources are acquired using a generic resource manager known as Framework component. See *MPEG4 Restricted Simple Profile Decoder on DM365 User's Guide* for details.

Code placement

All the algorithm code are placed in external memory. The performance quoted is not sensitive to algorithm code placement.

References

ISO/IEC 14496-2:2004, Information technology -- Coding of audio-visual objects -- Part 2: Visual (Approved in 2004-05-24)

MPEG4 Restricted Simple Profile Decoder on DM365 User's Guide (literature number: SPRUEV2A)

Glossary

TERM	DESCRIPTION
Constants	Elements that go into .const memory section
Scratch	Memory space that can be reused across different instances of the algorithm
Shared	Sum of Constants and Scratch
Instance	Persistent-memory that contains persistent information - allocated for each instance of the algorithm

Acronyms

ACRONYM	DESCRIPTION
CBR	Constant Bit Rate
CIF	Common Intermediate Format
CVBR	Constrained Variable Bit Rate
DP	Data Partitioning
EVM	Evaluation Module
HPI	Half Pel Interpolation
MJCP	MPEG4-JPEG Co-Processor
MV	Motion Vector
NV12	YUV 420 format with Y plane and CbCr plane
QP	Quantization Parameter
QCIF	Quarter Common Intermediate Format
QVGA	Quarter Video Graphics Array
RVLC	Reversible Variable Length Coding
SQCIF	Sub Quarter Common Intermediate Format
SSE	Sum of Square of Errors
SXVGA	Super eXtended Graphics Array
UMV	Unrestricted Motion Vectors

ACRONYM	DESCRIPTION
VBR	Variable Bit Rate
VGA	Video Graphics Array
VUI	Video Usability Information
XDM	eXpressDSP Digital Media

Revision History

There are no changes in the data sheet as compared to the previous version.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications
DSP	dsp.ti.com	Computers and Peripherals	www.ti.com/computers
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps
Interface	interface.ti.com	Energy	www.ti.com/energy
Logic	logic.ti.com	Industrial	www.ti.com/industrial
Power Mgmt	power.ti.com	Medical	www.ti.com/medical
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless-apps