

## H.264 High Profile Decoder (v01.10.00) on DM365

### FEATURES

- eXpressDSP™ Digital Media (XDM 1.2 IVIDDEC2) interface compliant
- Validated on DM365 EVM with MVL 5.0
- H.264 High Profile up to level 4.2 compliant (limited to maximum of 1920x1088 frame resolution)
- Both adaptive and sliding window DPB management supported
- Byte stream NAL unit format for input bit-stream
- Progressive, Field, PAFF and MBAff picture decoding supported
- Multiple slices and multiple reference frames supported
- CAVLC and CABAC decoding supported
- Main Profile features like B-Slice decoding and CABAC supported
- Weighted prediction for motion compensation in both P and B-slices supported
- Transform 8x8 mode, interspersed with transform 4x4 MBs supported
- Parsing and decoding with scaling lists present both in SPS and PPS NAL units supported
- Second chroma qp index offset value present in PPS supported
- All intra-prediction and inter-prediction modes supported
- Up to 16 MV per MB supported
- Output order conformance using frame bumping process supported
- Frame based decoding with frame size being multiples of 2 supported
  - Field based decoding with frame height being multiples of 4 supported

- Outputs are available in YUV420 interleaved big endian format
- Supplemental Enhancement Information (SEI) and Video Usability Information (VUI) supported
- Uses configurable frame display delay for out of order display
- Performs predictor based spatial and temporal error concealment on erroneous frames and reports the type of error occurred
- Supports up to 1080p (1920x1088) resolution.
- This version of the decoder does not support the following features:
  - Error concealment features such as ASO/FMO and redundant slices
  - Dynamic change in resolution
  - Raw NAL unit format for input bit-stream
  - Monochrome format in High Profile

### DESCRIPTION

H.264 (from ITU-T, also called as H.264/AVC) is a popular video coding algorithm enabling high quality multimedia services on a limited bandwidth network. H.264 standard defines several profiles and levels which specify restrictions on the bit-stream and hence limits the capabilities needed to decode the bit-streams. This project is developed using Code Composer Studio version 3.3.81.6 and using the code generation tools version 4.1.4.

PRODUCT PREVIEW



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

eXpressDSP is a trademark of Texas Instruments.

Linux is a registered trademark of Linus Torvalds.

Monta Vista is a registered trademark of MontaVista Software, Inc.

All other trademarks are the property of their respective owners.

PRODUCT PREVIEW information concerns products in the formative or design phase of development. Characteristic data and other specifications are design goals. Texas Instruments reserves the right to change or discontinue these products without notice.

Copyright © 2010, Texas Instruments Incorporated

## Performance Summary

This section describes the performance of Standalone H.264 High Profile Decoder validated on DM365 EVM resulting in performance equivalent to 30fps.

**Table 1. Configuration Table**

CONFIGURATION	ID
H.264 High Profile levels up to 4.2	H264_DEC_01

### Performance Measurement Procedure

- Measured with program memory and I/O buffers in external memory, I/D cache enabled, ARM @297 MHz, HDVICP @243 MHz, DDR @243 MHz, Monta Vista® Linux® 5.0
- Linux is used to measure the performance numbers in this Datasheet.
- The process time is measured across algActivate/process/algDeactivate function call using gettimeofday() utility of linux.
- NFS File system is used as an environment in performance measurement.

**Table 2. Cycles Information for H264\_DEC\_01**

INPUT NAME	RESOLUTION	PERFORMANCE STATISTICS (MEGA CYCLES) <sup>(1)</sup>					
		AVERAGE			PEAK		
		ARM926 PER FRAME	DECODE PER FRAME (ARM 926 and HDVICP)	FPS	ARM926 PER FRAME	DECODE PER FRAME (ARM 926 and HDVICP)	FPS
CIF_L1.2_384Kbps_15fps_news.264	CIF(352x288)	0.19	1.08	274.64	0.40	1.64	180.69
foreman_p640x480_30fps_420pl_300fr_1ref.264	VGA(640x480)	0.21	2.81	105.56	0.53	3.02	98.21
D1_football_720x480_384_30fBP.264	D1(720x480)	0.24	3.01	98.71	0.57	3.31	89.72
16MV_lpb_city_p1280x720_30fps_420pl_600fr.264	720p (1280 x 720)	0.20	8.47	35.08	0.50	9.83	30.20
720p50_parkrun_field1.264	720p (1280 x 720)	0.48	10.22	29.06	0.82	15.97	18.59
720p50_parkrun_mbaff.264	720p (1280 x 720)	0.30	13.20	22.50	0.63	15.63	19.00
colorful_toys_cif_5frms_420P.264	CIF(352x288)	0.37	1.20	246.30	0.67	1.41	209.23

(1) Average and peak values may vary by +/-5%.

**Table 3. Cycles Information for H264\_DEC\_01 for Closed Loop Configuration**

INPUT NAME	PERFORMANCE STATISTICS (MEGA CYCLES) <sup>(1)</sup>						
	RESOLUTION	AVERAGE			PEAK		
		ARM926 PER FRAME	DECODE PER FRAME (ARM 926 and HDVICP)	FPS	ARM926 PER FRAME	DECODE PER FRAME (ARM 926 and HDVICP)	FPS
akiyo_p352x288_30fps_420pl_300fr.264	CIF(352x288)	0.21	1.08	273.08	0.43	1.66	178.28
foreman_i640x480_30fps_420pl_300fr.264	VGA(640x480)	0.23	2.81	105.38	0.49	3.58	82.75
shields_p720x480_25fps_420pl_252fr.264	D1(720x480)	0.23	3.093	96.02	0.53	4.04	73.49
parkrun_p1280x720_30fps_420pl_300fr.264	720p (1280 x 720)	0.25	7.49	39.61	0.59	9.16	32.42

(1) Average and peak values may vary by +/-5%.

**Note:**

- Decode frame depicts the cumulative load on ARM926 and HDVICP.
- The values in [Table 2](#) and [Table 3](#) are as measured on the ARM926 side. These are the actual cycles as seen from the host on the DM365 EVM board and will be close to cycles seen on the final system (for average case).
- ARM926 represents mega cycles per frame spend on ARM926.
- Decode frame time is the time seen from ARM926 only. Since most of the processing happens at HDVICP, the active load on ARM926 is the value mentioned in ARM926 column. Decoder frame time has no connection with HDVICP running at 243 MHz.
- All the values are collected (both average and peak) at frame-level processing.
- They are measured with Linux without any system traffic.
- The version of the code used to collect these numbers have the following features included:
  - Interrupt mode of operation – one interrupt signal processing overhead per frame.
  - Resetting of HDVICP and loading of code into HDVICP program and data memory – once per stream.

**Table 4. Memory Statistics (Host ARM926 External Memory)**

CONFIGURATION ID	MEMORY STATISTICS (IN BYTES) <sup>(1)</sup>						
	PROGRAM MEMORY	DATA MEMORY				DPB FOR LEVEL 4.2 <sup>(3)</sup>	TOTAL
		CONSTANT <sup>(2)</sup>	HEAP		STACK		
			PERSISTENT <sup>(4)</sup>	SCRATCH			
H264_DEC_01	246036	324258	19036064	99200	16348	19000000	38821106

- (1) All these memory requirements are for ARM926 decoder library only. They do not include any memory requirements from test application side and input stream buffer. Stack, heap and code requirements for test-application are additional.
- (2) Constant memory size requirements include HDVICP program memory since it forms a constant table on ARM926 before transfer. The constant size is the sum of .cinit, .bss, and .const sections used by H.264 decoder library.
- (3) DPB for level 4.2 indicates tentative buffer requirements on the test application side to manage the DPB requirements of level 4.2 (however limited to the maximum resolution of 1920x1088) compliant H.264 decoder library implementing XDM1.2 API. DPB memory requirements given here include padding requirements along all dimensions (luma and packed chroma) assuming 4:2:0 format. It also includes memory required for holding the current frame. To enable optimal DMA transfers in the application, the picture width has been aligned to next 32-byte boundary. For eg: Padded and aligned 1080p picture would have a width of 1920 + 48 (Padding) + 16(alignment) = 1984. Because of these padding and alignment constraints, the DPB requirement for a normal picture would be different from that of its rotated version. The DPB requirement for some of the supported resolutions on the higher-end is given in [Table 5](#).
- (4) Persistent memory includes space required for 256 PPS and 32 SPS.

**Table 5. DPB Requirement (for level 4.2)**

RESOLUTION	DPB REQUIREMENT
1080p (1920x1088)	19000000

**Table 6. Internal Data Memory Split-Up**

CONFIGURATION ID	DATA MEMORY - HDVICP (IN BYTES)			
	HDVICP PROGRAM MEMORY	HDVICP DATA MEMORY	HDVICP BUFFERS	VICP (BYTES)
H264_DEC_01	48000	32000	ALL	55808

**Table 7. H264 Decoder DM365 Codec Usage of Memory Through CMEM**

BUFFER	YUV420P
Input Buffer <sup>(1)</sup>	0x200000 (Max)
Output Buffer	3523584
MEMTAB NUMBER	SIZE IN BYTES <sup>(2)</sup>
Memtab 0	1024
Memtab 1	14976
Memtab 2	14976
Memtab 3	2688
Memtab 4	8192
Memtab 5	18321120
Memtab 6	282624
Memtab 7	47752
Memtab 8	146116
Memtab 9	58144
Memtab 10	384
Memtab 11	10240
Memtab 12	65792
Memtab 13	30720

(1) The size of the input buffer should be equal to or greater than one frame data..

(2) The table has numbers for 1080p resolution.

The following CMEM allocations are dependent on the max width and max height and it provides the formula for calculating the size based on the input resolution:

- Output Buffer = Luma\_frameSize\_padded + Chroma\_frameSize\_padded  
where Luma\_frameSize\_padded = ((maxWidth + 48 + alignment)\*(maxHeight+ 96)). and Chroma\_frameSize\_padded = Luma\_frameSize\_padded / 2.
- Memtab 4 = 2 \* (((maxWidth + 4 \* 16) \* 2) + 8 + 127) & 0xFFFFFFF80)  
This is for storing the top rows for intra prediction. One for even row and one for odd row.
- Memtab 5 = Frame level collocated MB Info + Extra Frame Padding buffers  
where MB\_Info\_frame = (((maxWidth >> 4) + 1) \* (maxHeight >> 4)) + 1) \* (dpb\_limit at level 4.2 + 1). This is for storing ecd mb info data. and Frame\_Pad\_Buf = Luma\_Frame\_Pad\_Buf + Chroma\_Frame\_Pad\_Buf where Luma\_Frame\_Pad\_Buf = ((maxWidth + 48 + alignment)\*(48 + 1MB BB + 6) and Chroma\_Frame\_Pad\_Buf = Luma\_Frame\_Pad\_Buf / 2 Output Buffer maintains Field type padding only. Frame padding requires additional memory.

## Notes

- HDVICP and VICP
  - The entire HDVICP is a video resource and is used by the codec
  - The codec uses VICP memory as scratch buffers and hence there is restriction on the usage of VICP concurrently.
- DMA configuration

**Table 8. DMA Configuration**

TC Q's	TC 0	TC 1	TC 2	TC 3	TOTAL
Usage	Used by codec	Used by codec	Used by codec	Reserved for system	-
Priority	1	1	1	0	-
EDMA Channels	16	9	1	NA	26
PaRAM Entries	14	52	1	NA	67
QDMA Channels	0	0	0	NA	0

- The HDVICP/VICP/EDMA resources are acquired using a generic resource manager known as Framework Component. See *H.264 High Profile Decoder on DM365 User's Guide* for details.
- Code Placement
  - All the algorithm code are placed in external memory. The performance quoted is not sensitive to algorithm code placement.

## References

- ISO/IEC 14496-10:2005 (E) Rec. - Information technology – Coding of audio-visual objects – H.264 (E) ITU-T Recommendation.
- *H.264 High Profile Decoder on DM365 User's Guide* (literature number: SPRUEV0D)

## Glossary

TERM	DESCRIPTION
Constants	Elements that go into .const memory section
Scratch	Memory space that can be reused across different instances of the algorithm
Shared	Sum of Constants and Scratch
Instance	Persistent-memory that contains persistent information - allocated for each instance of the algorithm

## Acronyms

ACRONYM	DESCRIPTION
ASO	Arbitrary Slice Order
CIF	Common Intermediate Format
720p	1280x720 resolution
DMA	Direct Memory Access
DPB	Decoded Picture Buffer
EVM	Evaluation Module
FMO	Flexible Macro-block Ordering
HDVICP	High Definition Video and Imaging Co-Processor sub-system
PPS	Picture Parameter Set
SEI	Supplemental Enhancement Information
SPS	Sequence Parameter Set
VICP	Video and Imaging Co-Processor sub-system
VUI	Video Usability Information
XDM	eXpressDSP Digital Media

**Revision History**

There are no changes in the Data sheet for this release

**PRODUCT PREVIEW**

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>	Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>	Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>	Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>	Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>	Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>	Energy	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>	Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>	Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>	Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>	Space, Avionics & Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
RF/IF and ZigBee® Solutions	<a href="http://www.ti.com/lprf">www.ti.com/lprf</a>	Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
		Wireless	<a href="http://www.ti.com/wireless-apps">www.ti.com/wireless-apps</a>