

LMX9830DONGLE Hardware User Guide

1.0 Scope

Texas Instruments LMX9830 Bluetooth™ serial dongle reference design kit is a plug and play serial adapter for serial cable replacement applications and more. It is able to support more profiles than just the Serial Port Profile (including audio support with external codec boards). By using the enclosed Simply Blue Commander software, it allows user to develop their own SW applications easily given the built in interpreter for HEX commands. SBsmart is a higher level application tool that provides buttons with the built in commands to easily set up or demonstrate different profile support using the SimplyBlue SPP package.

2.0 General Description

2.1 REFERENCE DESIGN KIT CONTENTS

- LMX9830 Bluetooth serial adapter reference board
- USB Dongle and application software stack
- Null modem cable
- 110V to 240V AC to 5V DC power adapter and pigtail
- CDROM with design documents and SimplyBlue software Application tools.

2.2 LMX9830 BLUETOOTH SERIAL ADAPTER REFERENCE BOARD WITH CHIP ANTENNA ON BOARD




Figure 1. LMX9830 Serial Dongle Reference Board

Bluetooth is a trademark of Bluetooth SIG, Inc. and is used under license by Texas Instruments.

3.0 Requirement and Setup

3.1 BASIC REQUIREMENT

- X86 PC with serial port.
- One of the following operating system is required.
 - Windows XP
 - Windows 7

3.2 APPLICATION SOFTWARE

3.2.1 SimplyBlue Commander

Application command oriented tool to generate commands and watch events in the Simply Blue Command interface

window. Reference the Simply Blue Commander User Guide document for details.

3.2.2 SBSmart

Easy to use Windows based tool to demonstrate additional profile support of the SimplyBlue functionality. Reference the SBSmart User Guide for additional details.

3.2.3 Patch Programming

LMX9830 allows for patch programming for firmware update if necessary. Reference the LMX9830 SW User Guide document for details. Can also be done with the SimplyBlue Commander tool.




Figure 2. System Block Diagram

4.0 Functional Description

4.1 POWER SUPPLY

- DC Power Jack (6V max)
- Battery Holder (6V max)

4.2 MAIN SYSTEM

- Crystal - 13MHz
- Reset button for manual Reset
- Jumper option for Baud rate selection

4.3 UART INTERFACE

DB9 connector for RS232 standard PC interface using on-board level shifter IC for handling LMX9830 module's 3.3V UART interface.

4.4 ADVANCE AUDIO INTERFACE

- Support Audio applications
- PCM codec interface (support linear and A-law)
- PCM Master or Slave operation (SW configurable)

4.5 ANTENNA

- The Chip Antenna on board matched with RFinout of LMX9830 (50 ohm typ)
- Optional SMA connector for external antenna or direct cable for conducted measurements

5.0 Design Consideration

5.1 CARRIER FREQUENCY OFFSET

- Is highly dependant on the stability of main crystal (13MHz).
- Is recommended to be less than +/-20ppm over the entire operating temperature.

5.2 POWER MANAGEMENT

- 3.3V output single LDO is used to provide power for RS232 interface chip and digital portion of the LMX9830.

- 2.8V output single LDO is used to provide power for RF circuitry of the LMX9830.

5.3 ANTENNA DESIGN

- Chip Antenna is selected due to good price performance rating.
- Matching circuit is necessary and RFinout of LMX9830 is 50 ohm typical.
- Bandwidth of Antenna should be more than 100MHz (2.45GHz center frequency and VSWR<2).




Figure 3. S11 measurement on ANT pin

6.0 Layout Consideration

The LMX9830 reference design is split into 2 sections, one section is RS232 transceiver circuit for PC connection, another section is LMX9830 main circuit for Host processor. (Figure 4)

6.1 PCB REQUIREMENT

- 4 layers PCB required
- 1 mm overall thickness

6.2 LAYERS CLASSIFICATION

- Top layer is the components and main signals layer
- 2nd layer is ground plane
- 3rd layer is power plane
- Bottom layer is interface signals and ground plane
- RF circuit requirement
- Large ground plane with ground via's is must for good RF performance
- 50 ohm transmission line is used for matching between RFinout and Antenna
- T-network is designed for different type of Antenna matching
- Keep the maximum distance between main crystal and Antenna to avoid coupling of TDD signals from Antenna

7.0 Board components and Pin Assignments

A summary of the configuration and selection jumpers is provided in the tables that follow. Reference both the schematic and PCB layout (included on the CD in the kit)

Table 1 Major Components List

Device	Description
U1	64K EEPROM (access.bus)
U2	TI LMX9830 Serial Port Module - Reference the device datasheet.
U3	TI LP3985 Low-Dropout Voltage Regulator
U4	TI LP3985 Low-Dropout Voltage Regulator
U5	Maxim MAX3225 1 Mbps High Speed UART Driver
X1	13 MHz Crystal - Reference the crystal device datasheet and the LMX9830 datasheet for details.

Table 2 Connectors Summary

Connector	Description	Details
BAT1	Battery Connector 2mm pitch	Maximum input voltage is 6V
DC1	DC jack	Same as above
J1	DP9 serial connector (male)	See Table 7
J2	External processor interface	See Table 6
J3	Advance Audio interface	See Table 7

Table 3 Jumper and Test Point Summary

Jumper/Test Point	Description	Details
SMA	RF connector	Optional
P1	BBCLK	Test point for system clock
R15,16 and 18	Clock & UART setting jumper	See Table 8

Table 4 Switch and LEDs

Switch/LED	Description
SW3	Reset button
LED2	Operation Status
LED1	Data Traffic (TX/RX)

Table 5 J1 DP9 (male) Pin Assignments

Pin #	Signal name	Description
1	NC	No connection
2	RxD	Receive Data (input)
3	TxD	NC Transmit Data (output)
4	NC	No connection
5	GND	Ground
6	NC	No connection
7	RTS	Ready to send (output)
8	CTS	Clear to send (input)
9	NC	No connection

(Continued)

Table 8 UART interface setting (13MHz)

Open	Open	Short	NVS (9600bps)
------	------	-------	---------------

Table 6 J2 External Processor Interface

Pin #	Signal name	Description
1	LDO_CTL	ON/OFF control of LDO (input)
2	3V6	Power Supply, maximum 3.6V (input)
3	GND	Ground
4	UART_TX	Transmit Data (output)
5	UART_CTS	Clear to send (input)
6	UART_RX	Receive Data (input)
7	UART_RTS	Ready to send (output)
8	HOST_WU	Not used on LMX9830 - only used for LMX9820A
9	RESET	Reset (input)

Table 7 J3 Advance Audio Interface

Pin #	Signal name	Description
1	3VB	LDO output (2.8V)
2	AAI_SCLK	Advanced Audio Interface Clock
3	AAI_STD	Advanced Audio Interface Transmit Data
4	AAI_SFS	Advanced Audio Interface Frame Synchronization
5	AAI_SRD	Advanced Audio Interface Receive Data
6	GND	Ground

Table 8 UART interface setting (13MHz)

R15	R16	R18	UART baud rate
Short	Short	Short	921600bps (default)
Short	Open	Short	115200bps
Open	Short	Short	9600bps




Figure 4. Top view of Reference board

8.0 Bill of materials (Reference Board)

Item Name	Description	Vendor	Part Number
X1	TEW, TAS-4025A, 13.000MHz	TEW	20-A0058
X2	32.768kHz crystal	RALTRON	R26-32.768-12.5
ANT1	Chip Antenna	MuRata	ANCW12G45SAA117TT1
C1,C2	Capacitor 12p 0402 COG 50V	MuRata	GRM36COG120D50
C34,C35	Capacitor 22p 0402 COG 50V	MuRata	GRM36COG220J50
C3	Capacitor 100n 0402 Y5V16V	MuRata	GRM36Y5V104Z16
C4	Capacitor 2u2F0603 Y5V 10V	MuRata	GRM39Y5V225Z10
C5,C29,C33	Capacitor 10n 0402 X7R 50V	MuRata	GRM36X7R103K50
C27,C28	Capacitor 4p7 0402 COG 50V	MuRata	GRM36COG4R7J50
C6	Capacitor 8p2 0402 COG 50V	MuRata	GRM36COG8R2J50
C7	Capacitor 2200p 0402 X7R 50V	MuRata	GRM36X7R222K50
C8	Capacitor 220p 0402 COG 50V	MuRata	GRM36COG221J50
C9	Capacitor 39p 0402 COG 50V	MuRata	GRM36COG390J50
C10	Capacitor 1n 0402 X7R 16V	MuRata	GRM36X7R102K16
C26,C30,C31, C32	Capacitor 100n 0402 X7R 16V	MuRata	GRM36X7R104K16
C13,C14,C17	Capacitor 10n 0603 X7R 50V	MuRata	GRM39X7R102K50
C18	Capacitor 100n 0603 X7R 16V	MuRata	GRM39X7R104K50
C16	Capacitor 100p 0603 COG 50V	MuRata	GRM39COG101J50
C19,C22	TANT CAP 1uF 6.3V SIZE A	Any	
C12,C15	TANT CAP 2.2uF 6.3V SIZE A	Any	
C11,C20,C21, C23,C24	Capacitor 1uF 1206 X7R 25V	MuRata	GRM42-6X7R105K25
L1	Chip Inductor 2N2 0603	MuRata	LQG18HN2N2S00
L2	Chip Inductor 3N9 0603	MuRata	LQG18HN3N9S00
BAT1	Battery holder (2mm pitch)	Any	
SW3	TACK SWITCH TS-1135HS	RAINBOW	
DC1	DC POWER JACK	Morning string limited	DC-015
LED2	Red Color LED 0603 Size	Any	
LED1	Blue Color LED 0603 Size	Any	
J1	DB9 (male) serial connector	Any	
J3	2mm Header (6 poles)	Any	
U1	64K EEPROM	ATMEL	AT24C64A-10TI-1.8
U2	Bluetooth SPP Micro Module	Texas Instruments	LMX9830SM
U3	Low Dropout Regulator	Texas Instruments	LP3985IM5-3.3
U4	Low Dropout Regulator	Texas Instruments	LP3985IM5-2.8
U5	High Speed RS232 Transceivers	Maxim	MAX3225EEAP
R17	Resistor 0603 Size, 1K	Any	
R3,R4	Resistor 0603 Size, 10K	Any	
R8,R9,R10,R 11,R19,R20,R 21,R22	Resistor 0603 Size, 0R	Any	
R2,R7,R28,R 29	Resistor 0402 Size, 1K	Any	
R13,R25	Resistor 0402 Size, 330R	Any	

(Continued)

Item Name	Description	Vendor	Part Number
R14,R17	Resistor 0402 Size, 10K	Any	
R23	Resistor 0402 Size, 3K3	Any	
R26,C35	Resistor 0402 Size, 0R	Any	
R31	Resistor 0402 Size, 100K	Any	
R16	2mm header	Any	
R15, R18	2mm header (with jumper)	Any	

9.0 References

- LMX9830 Bluetooth Serial Port Module data sheet
- LMX9830 Bluetooth Serial Port Module - Software Users Guide
- SBSmart user guide

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com