

LMX9838 Design Guide


Texas Instruments Incorporated
Application Note 1587
Sebastien Mathieu
September 2007
Revised February 2013



1.0 Scope

This application note provides guidelines for designing with the LMX9838 Bluetooth Serial Port Module, particularly for critical aspects of the PCB layout. The guidelines have been organized in a simplified flow that walks you through the first steps on what documentation to review, key design considerations and then the final steps of certification and production.

Since the antenna is integrated in to the module, the PCB layout and placement of the LMX9838 is critical in order to maximize performance (i.e. range and data throughput). The key sections to review before laying out a PCB are Section 5.0 and the document [4].



CompactRISC is a trademark of Texas Instruments Incorporated. Bluetooth is a trademark of Bluetooth SIG, Inc. and is used under license by Texas Instruments Incorporated.

Table Of contents

1.0 Scope	1
2.0 Device introduction	3
3.0 Product design flow	3
3.1 Documentation	3
3.2 Key design considerations	3
3.3 Certification and Registration	3
4.0 Design flow details	3
4.1 Documentation structure	3
4.1.1 Design documents	3
5.0 PCB Design details	4
5.1 Module Placement	4
5.2 Schematic	5
5.3 Layout	6
5.4 Design considerations	7
6.0 Most common design errors	8
7.0 Certification and registration	8
7.1 Bluetooth Conformance Testing	8
8.0 Bibliography	9

2.0 Device introduction

The Texas Instruments LMX9838 Bluetooth Serial Port module is a fully integrated Bluetooth 2.0 base band controller, 2.4 GHz radio, crystal, antenna, LDO and discreet; combined to form a complete small form factor Bluetooth node.

All hardware and firmware is included to provide a complete solution from antenna through the complete lower and upper layers of the Bluetooth stack, up to the application including the Generic Access Profile (GAP), the Service Discovery Application Profile (SDAP), and the Serial Port Profile (SPP). The module includes a configurable service database to fulfill service requests for additional profiles on the host. Moreover, the LMX9838 is pre-qualified as a Bluetooth subsystem. Conformance testing through the Bluetooth qualification program enables a short time to market after system integration by insuring a high probability of compliance and interoperability.

Based on TI's CompactRISC™ 16-bit processor architecture and Digital Smart Radio technology, the LMX9838 is optimized to handle the data and link management processing requirements of a Bluetooth node.

The firmware supplied in the on-chip ROM memory offers a complete Bluetooth (v2.0) stack including profiles and command interface. This firmware features point-to-point and point-to-multipoint link management supporting data rates up to the theoretical maximum over RFSComm of 704 kbps. The internal memory supports up to 7 active Bluetooth data links and one active SCO link.

The on-chip Patch RAM provided for lowest cost and risk, allows the flexibility of firmware upgrade.

The module is lead free and RoHS (Restriction of Hazardous Substances) compliant. For more information on those quality standards, please visit <http://www.ti.com>.

3.0 Product design flow

3.1 DOCUMENTATION

- LMX9838 Datasheet [1]
- LMX9838 Design Guide [2]
- LMX9838 Software User's Guide [3]
- LMX9838 Placement Application Note[4]

3.2 KEY DESIGN CONSIDERATIONS

- Power supply decoupling - refer to [1]
- Integrated Antenna Properties and Design Guidelines - refer to [4]
- Low power mode - refer to [1]

3.3 CERTIFICATION AND REGISTRATION

- Certification - refer to Section 7.0

4.0 Design flow details

4.1 DOCUMENTATION STRUCTURE

4.1.1 Design documents

- 1) LMX9838 Design Guide [2] (this document): contains design key points and recommendations for a system implementing the LMX9838.
- 2) LMX9838 Datasheet [1]: contains key performance details regarding the device, pin description, functional details, programming details, package information and applications information.
- 3) LMX9838 Software User's Guide [3]: The document is a reference for implementing the LMX9838 module into a system. A getting started session gives a very detailed entry point for starting software development. The advance usage section describes all features and configuration parameters in detail and gives example for using the LMX9838 as active Bluetooth node. Finally all commands and events are listed and explained in the command section.

5.2 SCHEMATIC




Figure 2. LMX9838 implementation example

5.3 LAYOUT




Figure 3. LMX9838 module placement example

Key points to consider for the schematic and layout design are listed below:

Table 1. Design key points

1	Decoupling capacitors
2	Advanced audio interface connect to PCM codec or leave open
3	32Khz crystal for low power mode, see [1]
4	Frequency baud rate selector and GPIO's
5	Ground connections and Ground vias
6	FR4 only area. Keep metal out of this area.

Table 2. Soldering recommendation

7	Inner area of module shall be left empty, do not solder the inner pads of the module
8	Vias should be placed outside the module outline to avoid raising the package corner, which will prevent the package from sitting flat and creating problems for soldering
-	All traces connecting to the soldering pads should be the same width in order to equalize the metal area for soldering. Specifically connections to pads 3, 4, 29, 30, 31 and 32. Tangential connections to the pads should be avoided

Table 2. Soldering recommendation

-	The solder paste stencil artwork should be arranged so that the pad openings are 0.1mm outwards, generating what is called a "stencil pullback". This helps center the package during reflow, creates an external "fillet" and prevents any shorts on the corner pads by increasing the space between paste openings
-	The silkscreen outline for the module should be placed outwards so that the ink does not raise the component up and also so that the ink does not get too close to the soldering pads
-	Designators should not be placed under the module outline

Table 3. FR4 PCB Thickness recommendation

-	It is recommended to use the FR4 PCB with a thickness between 30 mil (0.76mm) and 100 mil (2.54mm). Optimum antenna performance is achieved using 60 mil (1.52mm).
---	--

Table 4. Proximity recommendation


-	It is recommended to keep metal objects no closer than 30mm away from the antenna end of the LMX9838 module to minimize field pattern modification and performance degradation.
-	Do not use a shielded RF enclosure. The enclosure must allow the antenna to radiate thru.

5.4 DESIGN CONSIDERATIONS

- Ideally a decoupling capacitor pair should be used per VCC pin of the device. It is recommended to use a 2.2 μ F and 100nF together. Single capacitors maybe used in some cases without significantly degrading performance. The capacitors should be placed as close as is physically possible to the module's respective pins.
- One solid Bluetooth ground plane shall be used for all ground pins on the module. It is recommended to place

this ground plane on the layer immediately under the top layer. The size of the ground plane only has to be as large as the module and the modules supporting components.

- The Bluetooth ground plane is typically separated from the other system ground planes to reduce coupling of noise in to the Bluetooth module or from the Bluetooth module in to sensitive circuitry.

**Figure 4. System ground planes**

For example, if there is additional digital circuitry sharing the same printed circuit board then it is advisable to create a separate digital ground plane and Bluetooth ground plane as in Figure 4. The ground planes should not overlap and should be positioned as close as possible to each other. They should be connected together at a single point.

- For the internal antenna in the module to operate to its maximum efficiency then the PCB area around the antenna should be cut away. It is recommended to place the end of the module flush to the edge of the PCB and to route the PCB out around the antenna end, see Figure 1.

- Digital signals to/from the module are typically routed on the top layer of the board but should be kept away from the antenna end of the module to avoid cross-talk problems. Digital signals can be routed underneath the module but they must be routed under the ground plane (to reduce cross-talk in to the module) and then come through the ground plane to the top layer. Having too many vias in a close area perforating the ground plane will reduce the effectiveness of the ground plane. Therefore use them sparingly.
- A 32.768KHz oscillator maybe used to support lower power mode for reduced power consumption. The modular structure of the LMX9838 allows the firmware to power down unused modules such as the radio LLC and UART interface. Refer to [1] for further information.

6.0 Most common design errors

Since the LMX9838 is a highly integrated module with internal tuned crystal and antenna, there is little room for error in terms of PCB layout. However, some common customer errors that have occurred in the past are listed here.

Non Compact Design

When there is more than enough space on the PCB which must be of a certain shape and size to conform to the application, customers tend to spread the external components over a larger area than is required. This is a mistake, though there maybe space available, the external components such as decoupling capacitors, etc must be placed as close to the LMX9838 as possible otherwise this will result in degraded performance due to unnecessary line parasitic.

Long lines also cause cross-coupling and spurious emissions.

Poor grounding

Not using enough ground vias or ground lines that are too thin and long is a common error. Long tracks are inductive causing the grounding point to sit at a higher voltage (at 2.4GHz) than the ground plane.

Not enough clearance around internal antenna

The internal antenna must be kept clear of any components and especially copper ground plane that can detune it (see Section 5.0). A detuned antenna will result in bad return loss into it and ultimately decreased range of operation.

7.0 Certification and registration

7.1 BLUETOOTH CONFORMANCE TESTING

The LMX9838 has been fully certified to Bluetooth core specification 2.0 through SPP (Serial Port Profile) as an end-product. If SPP is used then no further testing is required, however, if the customer decides to implement another profile then the customer should contact the BQB (Bluetooth Qualification Body) to see if any additional interoperability testing is required.

For example, if a customer uses the LMX9838 as pure slave device, with no additional profile on top, there will be no additional qualification required and therefore no testing costs AND no listing fee. If the customer uses the LMX9838 as active master, it might be necessary to at least do some interoperability tests, to make sure the interface is used correctly - this decision will depend on the BQB. Also, if additional profiles are used on the host, it needs to be qualified as well.

For more detailed information on certification and regulatory testing refer to [5].

8.0 Bibliography

- [1] LMX9838 Datasheet: Technical document explaining the LMX9838 features, pinout, characteristics, and soldering informations.
- [2] AN-1587: LMX9838 Design Guide: This document.
- [3] AN-1699: LMX9838 Software User's Guide: Document exploring in details the LMX9838 firmware functionalities, the embedded language interface, and a few interesting scenarios such as incoming link, multiple links, audio links, DUN profile, Headset and Handsfree profiles.
- [4] AN-1701: LMX9838 Placement Application Note: Document concentrating on the antenna backgrounds demonstrating the best physical placement of the LMX9838 on a printed circuit board.
- [5] AN-1709: LMX9838 Qualification Document: Gives a brief overview of the qualification steps required for a converting a LMX9838 design to an end product.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com